


Overview

- Ricoh Imaging lens
- 12 mm
- F 2.0-16
- format 1,1"
- M.O.D. 0.08 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 57,5 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 60.5 mm

Weight ≤ 156 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP

Focal length 12 mm

Focal range ≥ 12 mm ... < 25 mm

Format 1,1"

Aperture F2.0-16

Aperture control Manual

M.O.D. 0.08 m