

ZVL-FL-BC2518-9M

Article number: 11154325

Overview

- Ricoh Imaging lens
- 25 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 57,5 mm

Max. outer diameter 42 mm (without knurled screws)

52 mm (with knurled screws)

Max. length (excl. thread) 57.5 mm

Weight ≤ 149 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP

Focal length 25 mm

Focal range ≥ 25 mm ... < 50 mm

Format 1,1"

Aperture F1,8-16

Aperture control Manual

M.O.D. 0.1 m