

Overview

- Ricoh Imaging lens
- 35 mm
- F 1,6-16
- format 1,1"
- M.O.D. 0,15 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 60,2 mm
 Max. outer diameter 42 mm (without knurled screws)
 52 mm (with knurled screws)
 Max. length (excl. thread) 60.2 mm
 Weight ≤ 150 g
 Filter thread M 40,0 × 0,5

Lens data

Lens resolution 12 MP
 Focal length 35 mm
 Focal range ≥ 25 mm ... < 50 mm
 Format 1,1"
 Aperture F1,8-16
 Aperture control Manual
 M.O.D. 0.15 m