

ZVL-FL-BC5024-9M

Article number: 11154327

Overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 1,1"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 69,0 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 69 mm

Weight ≤ 166 g

Filter thread M 40,0 × 0,5

Lens data

Lens resolution 12 MP

Focal length 50 mm

Focal range ≥ 50 mm

Format 1,1"

Aperture F2,4-22

Aperture control Manual

M.O.D. 0.2 m