

ZVL-FL-BC5024-9M

Article number: 11154327

Overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 1,1"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 69,0 mm
 Max. outer diameter 42 mm (without knurled screws)
 52 mm (with knurled screws)
 Max. length (excl. thread) 69 mm
 Weight ≤ 166 g
 Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP
 Focal length 50 mm
 Focal range ≥ 50 mm
 Format 1,1"
 Aperture F2,4-22
 Aperture control Manual
 M.O.D. 0.2 m