

Overview

- Ricoh Imaging lens
- 75 mm
- F 2,8-32
- format 1,1"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 42 mm × 81,0 mm

Max. outer diameter 42 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 81 mm

Weight ≤ 189 g

Filter thread M 40,0 × 0,5

Lens data

Lens resolution 12 MP

Focal length 75 mm

Focal range ≥ 50 mm

Format 1,1"

Aperture F2,8-32

Aperture control Manual

M.O.D. 0.25 m