

**overview**

- Ricoh Imaging lens
- 6 mm
- F 1,4-16
- format 1/2"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



**technical data**

**general data**

manufacturer Ricoh Imaging

**mechanical data**

lens mount C-mount

dimensions 48 mm × 59,9 mm

max. outer diameter 48 mm (without knurled screws)  
50 mm (with knurled screws)

max. length (excl. thread) 59,9 mm

weight ≤ 149 g

**lens data**

lens resolution 2 MP

focal length 6 mm

format 2/3"

aperture F1,4-16

aperture control manual

M.O.D. 0,1 m