

ZVL-FL-CC0814A-2M

Article number: 11150223

Overview

- Ricoh Imaging lens
- 8 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 36,7 mm
 Max. outer diameter 42 mm (without knurled screws)
 45 mm (with knurled screws)
 Max. length (excl. thread) 36.7 mm
 Weight ≤ 76 g

Mechanical data

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 2 MP
 Focal length 8 mm
 Format 2/3"
 Aperture F1,4-16
 Aperture control Manual
 M.O.D. 0.1 m