

## ZVL-FL-CC1614-2M

Article number: 10170039

### Overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



### Technical data

#### General data

Manufacturer Ricoh Imaging

#### Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 33,2 mm

Max. outer diameter 29.5 mm (without knurled screws)  
39.5 mm (with knurled screws)

Max. length (excl. thread) 33.2 mm

Weight ≤ 63 g

Filter thread M 27,0 × 0,5

#### Lens data

Lens resolution 2 MP

Focal length 16 mm

#### Lens data

Focal range ≥ 12 mm ... < 25 mm

Format 2/3"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.25 m

Horizontal angle of view 31 °

Vertical angle of view 23.4 °

Diagonal angle of view 38.3 °

At image format 8,8 × 6,6 mm

#### Environmental conditions

Operating temperature -20 ... +50 °C