

Overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount	C-mount
Dimensions	29,5 mm × 32,2 mm
Max. outer diameter	29.5 mm (without knurled screws) 39.5 mm (with knurled screws)
Max. length (excl. thread)	32.2 mm
Weight	≤ 54 g
Filter thread	M 27,0 × 0,5

Lens data

Lens resolution	2 MP
Focal length	16 mm
Focal range	≥ 12 mm ... < 25 mm
Format	2/3"
Aperture	F1,4-16
Aperture control	Manual
M.O.D.	0.1 m