

overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-22
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- compact size (Ø 30,0 mm)
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 30 mm × 33 mm

max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

max. length (excl. thread) 33 mm

weight ≤ 58 g

filter thread M 27,0 × 0,5

lens data

lens resolution 0,3 MP

focal length 16 mm

lens data

focal range ≥ 12 mm ... < 25 mm

format 2/3"

aperture F1,4-22

aperture control manual

M.O.D. 0,3 m

horizontal angle of view 30,7 °

vertical angle of view 23,2 °

diagonal angle of view 38,2 °

at image format 8,8 × 6,6 mm

environmental conditions

operating temperature -20 ... +50 °C