

## ZVL-FL-CC2514-2M

Article number: 11002222

### Overview

- Ricoh Imaging lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



### Technical data

#### General data

Manufacturer Ricoh Imaging

#### Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 32,0 mm

Max. outer diameter 29.5 mm (without knurled screws)  
39.5 mm (with knurled screws)

Max. length (excl. thread) 32 mm

Weight ≤ 55 g

Filter thread M 27,0 × 0,5

#### Lens data

Lens resolution 2 MP

Focal length 25 mm

#### Lens data

Focal range ≥ 25 mm ... < 50 mm

Format 2/3"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.25 m

Horizontal angle of view 20 °

Vertical angle of view 15.1 °

Diagonal angle of view 24.9 °

At image format 8,8 × 6,6 mm

#### Environmental conditions

Operating temperature -20 ... +50 °C