

**overview**

- Ricoh Imaging lens
- 25 mm
- F 1,4
- format 2/3"
- M.O.D. 0,1 m
- C-mount
- Phase-Out starting 08/20, alternative via sales



**technical data**

**general data**

manufacturer Ricoh Imaging

**mechanical data**

lens mount C-mount

dimensions 43 mm × 44 mm

max. outer diameter 43 mm (without knurled screws)  
53 mm (with knurled screws)

max. length (excl. thread) 44 mm

weight ≤ 130 g

filter thread M 40,5 × 0,5

**lens data**

lens resolution 5 MP

focal length 25 mm

**lens data**

focal range ≥ 25 mm ... < 50 mm

format 2/3"

aperture F1,4

aperture control manual

M.O.D. 0,1 m

horizontal angle of view 19,9 °

vertical angle of view 15 °

diagonal angle of view 24,7 °

at image format 8,8 × 6,6 mm

**environmental conditions**

operating temperature -20 ... +50 °C