

**Overview**

- Ricoh Imaging lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



**Technical data**

**General data**

Manufacturer Ricoh Imaging

**Mechanical data**

Lens mount C-mount  
 Dimensions 32 mm × 38 mm  
 Max. outer diameter 32 mm (without knurled screws)  
 42 mm (with knurled screws)  
 Max. length (excl. thread) 38 mm  
 Weight ≤ 63 g

**Mechanical data**

Filter thread M 30,0 × 0,5

**Lens data**

Lens resolution 2 MP  
 Focal length 25 mm  
 Format 2/3"  
 Aperture F1,4-16  
 Aperture control Manual  
 M.O.D. 0.1 m