

Overview

- Ricoh Imaging lens
- 25 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 32 mm × 38 mm
 Max. outer diameter 32 mm (without knurled screws)
 42 mm (with knurled screws)
 Max. length (excl. thread) 38 mm
 Weight ≤ 63 g

Mechanical data

Filter thread M 30,5 × 0,5

Lens data

Lens resolution 2 MP
 Focal length 25 mm
 Format 2/3"
 Aperture F1,4-16
 Aperture control Manual
 M.O.D. 0.1 m