

## ZVL-FL-CC3516-2M

Article number: 11003417

### Overview

- Ricoh Imaging lens
- 35 mm
- F 1,6-16
- format 2/3"
- M.O.D. 0,35 m
- locating screw for aperture and focus
- C-mount



### Technical data

#### General data

Manufacturer Ricoh Imaging

#### Mechanical data

Lens mount C-mount  
 Dimensions 29,5 mm × 35,4 mm  
 Max. outer diameter 29.5 mm (without knurled screws)  
 39.5 mm (with knurled screws)  
 Max. length (excl. thread) 35.4 mm  
 Weight ≤ 64 g  
 Filter thread M 27,0 × 0,5

#### Lens data

Lens resolution 2 MP  
 Focal length 35 mm

#### Lens data

Focal range ≥ 25 mm ... < 50 mm  
 Format 2/3"  
 Aperture F1,6-16  
 Aperture control Manual  
 M.O.D. 0.45 m  
 Horizontal angle of view 14.8 °  
 Vertical angle of view 11.1 °  
 Diagonal angle of view 18.4 °  
 At image format 8,8 × 6,6 mm

#### Environmental conditions

Operating temperature -20 ... +50 °C