

# ZVL-FL-CC5024A-2M

Article number: 11150230

## Overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Ricoh Imaging

### Mechanical data

Lens mount C-mount  
 Dimensions 32 mm × 46,5 mm  
 Max. outer diameter 32 mm (without knurled screws)  
 42 mm (with knurled screws)  
 Max. length (excl. thread) 46.5 mm  
 Weight ≤ 66 g

### Mechanical data

Filter thread M 30,5 × 0,5

### Lens data

Lens resolution 2 MP  
 Focal length 50 mm  
 Format 2/3"  
 Aperture F2,4-22  
 Aperture control Manual  
 M.O.D. 0.3 m