

## ZVL-FL-CC5028-2M

Article number: 11012785

### overview

- Ricoh Imaging lens
- 50 mm
- F 2,8-22
- format 2/3"
- M.O.D. 0,9 m
- locating screw for aperture and focus
- C-mount



### technical data

#### general data

manufacturer Ricoh Imaging

#### mechanical data

lens mount C-mount

dimensions 29,5 mm × 34,0 mm

max. outer diameter 29,5 mm (without knurled screws)  
39,5 mm (with knurled screws)

max. length (excl. thread) 34 mm

weight ≤ 55 g

filter thread M 27,0 × 0,5

#### lens data

lens resolution 2 MP

focal length 50 mm

#### lens data

focal range ≥ 50 mm

format 2/3"

aperture F2,8-22

aperture control manual

M.O.D. 0,9 m

horizontal angle of view 10,1 °

vertical angle of view 7,6 °

diagonal angle of view 12,5 °

at image format 8,8 × 6,6 mm

#### environmental conditions

operating temperature -20 ... +50 °C