

ZVL-FL-CC7528-2M

Article number: 11003041

Overview

- Ricoh Imaging lens
- 75 mm
- F 2,8 32
- format 2/3"
- M.O.D. 0,7 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 34 mm × 59,6 mm

Max. outer diameter 34 mm (without knurled screws)
44 mm (with knurled screws)

Max. length (excl. thread) 59.6 mm

Weight ≤ 125 g

Filter thread M 30,5 × 0,5

Lens data

Lens resolution 2 MP

Focal length 75 mm

Lens data

Focal range ≥ 50 mm

Format 2/3"

Aperture F2,8-32

Aperture control Manual

M.O.D. 0.7 m

Horizontal angle of view 6.9 °

Vertical angle of view 5.2 °

Diagonal angle of view 8.6 °

At image format 8,8 × 6,6 mm

Environmental conditions

Operating temperature -20 ... +50 °C