

ZVL-FL-HC0614-2M

Article number: 11008992

Overview

- Ricoh Imaging lens
- 6 mm
- F 1,4-16
- format 1/2"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 32 mm × 37,5 mm

Max. outer diameter 32.6 mm (without knurled screws)
42.5 mm (with knurled screws)

Max. length (excl. thread) 37.5 mm

Weight ≤ 65 g

Filter thread M 30,5 × 0,5

Lens data

Lens resolution 2 MP

Focal length 6 mm

Focal range < 12 mm

Format 1/2"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 57.4 °

Environmental conditions

Operating temperature -20 ... +50 °C