

ZVL-FL-HC1212B-VG

Article number: 11012527

overview

- Ricoh Imaging lens
- 12 mm
- F 1,2-22
- format 1/2"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



technical data

general data

manufacturer Ricoh Imaging

mechanical data

lens mount C-mount

dimensions 30 mm × 35,5 mm

max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

max. length (excl. thread) 35,5 mm

weight ≤ 67 g

filter thread M 27,0 × 0,5

lens data

lens resolution 0,3 MP

focal length 12 mm

lens data

focal range ≥ 12 mm ... < 25 mm

format 1/2"

aperture F1,2-22

aperture control manual

M.O.D. 0,2 m

horizontal angle of view 30,2 °

vertical angle of view 22,6 °

diagonal angle of view 37,8 °

at image format 6,4 × 4,8 mm

environmental conditions

operating temperature -20 ... +50 °C