

ZVL-FL-HC1212B-VG

Article number: 11012527

Overview

- Ricoh Imaging lens
- 12 mm
- F 1,2-22
- format 1/2"
- M.O.D. 0,2 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 30 mm × 35,5 mm

Max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

Max. length (excl. thread) 35.5 mm

Weight ≤ 67 g

Filter thread M 27,0 × 0,5

Lens data

Lens resolution 0.3 MP

Focal length 12 mm

Lens data

Focal range ≥ 12 mm ... < 25 mm

Format 1/2"

Aperture F1,2-22

Aperture control Manual

M.O.D. 0.2 m

Horizontal angle of view 30.2 °

Vertical angle of view 22.6 °

Diagonal angle of view 37.8 °

At image format 6,4 × 4,8 mm

Environmental conditions

Operating temperature -20 ... +50 °C