

## ZVL-FL-HC1214-2M

Article number: 11004362

### overview

- Ricoh Imaging lens
- 12 mm
- F 1,4-16
- format 1/2"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



### technical data

#### general data

manufacturer Ricoh Imaging

#### mechanical data

lens mount C-mount

dimensions 29,5 mm × 28,5 mm

max. outer diameter 29,5 mm (without knurled screws)  
39,5 mm (with knurled screws)

max. length (excl. thread) 28,5 mm

weight ≤ 55 g

filter thread M 27,0 × 0,5

#### lens data

lens resolution 2 MP

focal length 12 mm

#### lens data

focal range ≥ 12 mm ... < 25 mm

format 1/2"

aperture F1,4-16

aperture control manual

M.O.D. 0,25 m

horizontal angle of view 28,9 °

vertical angle of view 22,9 °

diagonal angle of view 35,7 °

at image format 6,4 × 4,8 mm

#### environmental conditions

operating temperature -20 ... +50 °C