

Overview

- Ricoh Imaging lens
- 35 mm
- F 2,8-22
- format 45 mm
- M.O.D. 0,19 m
- locating screw for aperture and focus
- F-mount



Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount F-Mount

Dimensions 72 mm × 56,8 mm

Max. outer diameter 72 mm (without knurled screws)
82 mm (with knurled screws)

Max. length (excl. thread) 56.8 mm

Weight ≤ 380 g

Filter thread M 62,0 × 0,75

Lens data

Lens resolution 48 MP

Focal length 35 mm

Focal range ≥ 25 mm ... < 50 mm

Format 45 mm

Aperture F2,8-22

Aperture control Manual

M.O.D. 0.19 m