

Overview

- Computar lens
- 6 mm
- F 2,4
- format 1/2"
- M.O.D. 0,1 m
- S-mount



Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount S-mount

Dimensions 17 mm × 20,5 mm

Max. length (excl. thread) 6.5 mm

Weight ≤ 7 g

Lens data

Lens resolution 2 MP

Focal length 6 mm

Lens data

Focal range < 12 mm

Format 1/2"

Aperture F2,4

M.O.D. 0.1 m

Horizontal angle of view 59.1 °

Vertical angle of view 45 °

Diagonal angle of view 72.5 °

At image format 12.2 × 8,9 mm

Environmental conditions

Operating temperature -20 ... +50 °C