

Overview

- Computar lens
- 6 mm
- F 2,4
- format 1/2"
- M.O.D. 0,1 m
- S-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount S-mount
 Dimensions 17 mm × 20,5 mm
 Max. length (excl. thread) 6.5 mm
 Weight ≤ 7 g

Lens data

Lens resolution 2 MP
 Focal length 6 mm

Lens data

Format 1/2"
 Aperture F2,4
 M.O.D. 0.1 m
 Horizontal angle of view 59.1 °
 Vertical angle of view 45 °
 Diagonal angle of view 72.5 °
 At image format 12.2 × 8,9 mm

Environmental conditions

Operating temperature -20 ... +50 °C