

ZVL-LM12JC10M

Article number: 11193127

Overview

- Kowa lens
- 12 mm
- F 1,8-11
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount
 Dimensions 33 mm × 53.5 mm
 Max. outer diameter 33 mm (without knurled screws)
 40 mm (with knurled screws)
 Max. length (excl. thread) 53.5 mm
 Weight ≤ 105 g
 Filter thread M 25,5 × 0,5

Lens data

Focal length 12 mm

Lens data

Focal range ≥ 12 mm ... < 25 mm
 Format 2/3"
 Aperture F1,8-11
 Aperture control Manual
 M.O.D. 0.1 m
 Horizontal angle of view 39.1 °
 Vertical angle of view 29.8 °
 Diagonal angle of view 47.8 °
 At image format 6,6 × 8,8 mm

Environmental conditions

Operating temperature -10 ... +50 °C