

## ZVL-LM3NCM 3,5mm/f2,4

Article number: 11116658

### overview

- Kowa lens
- 3,5 mm
- F 2,4-14
- format 1/1.8"
- M.O.D. 0,1 m
- C-mount



### technical data

#### general data

manufacturer Kowa

#### mechanical data

lens mount C-mount

dimensions 42 mm × 38,2 mm

max. outer diameter 42 mm (without knurled screws)  
52 mm (with knurled screws)

max. length (excl. thread) 38,2 mm

weight ≤ 85 g

filter thread M 40,5 × 0,5

#### lens data

lens resolution 2 MP

focal length 3,5 mm

focal range < 12 mm

format 1/1.8"

aperture F2,4-14

aperture control manual

M.O.D. 0,1 m