

ZVL-LM6HC

Article number: 11215056

Overview

- Kowa lens
- 6 mm
- F 1,8-16
- format 1"
- M.O.D. 0,1 m
- C-mount



Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 54 mm × 56,6 mm

Max. outer diameter 54 mm (without knurled screws)
54 mm (with knurled screws)

Max. length (excl. thread) 56.6 mm

Weight ≤ 215 g

Lens data

Lens resolution 7 MP

Pixel resolution 5 µm

Focal length 6 mm

Lens data

Focal range < 12 mm

Format 1"

Aperture F1,8-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 96.8 °

Vertical angle of view 79.4 °

Diagonal angle of view 108.4 °

At image format 12,8 × 9,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C

Storage temperature -20 ... +60 °C