

ZVL-LM6JC

Article number: 11178763

Overview

- Kowa lens
- 6 mm
- F 1,4 - 16
- format 2/3"
- M.O.D. 0,1 m
- C-mount



Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions Ø 30 mm × 32,8 mm

Max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

Max. length (excl. thread) 32.8 mm

Weight ≤ 63 g

Lens data

Lens resolution 2.3 MP

Pixel resolution 5 µm

Focal length 6 mm

Lens data

Focal range < 12 mm

Format 2/3"

Aperture F1,4 - 16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 81.9 °

Vertical angle of view 61.2 °

Diagonal angle of view 102.9 °

At image format 6,6 × 8,8 mm

Environmental conditions

Operating temperature -10 ... +45 °C