

ZVL-LSF10528-U58

Article number: 11205387

Overview

- Myutron lens
- 105 mm
- F 2,8-22
- format 46 mm
- M.O.D. 0,43 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount M58-mount

Dimensions 80 mm × 163 mm

Max. outer diameter 80 mm (without knurled screws)
90 mm (with knurled screws)

Max. length (excl. thread) 159 mm

Weight ≤ 782 g

Filter thread M 62,0 × 0,75

Lens data

Lens resolution 48 MP

Focal length 105 mm

Focal range ≥ 50 mm

Format 46 mm

Aperture F2,8-22

Aperture control Manual

M.O.D. 0.43 m

Environmental conditions

Operating temperature 0 ... +40 °C