

ZVL-LSF20035-U58

Article number: 11205388

Overview

- Myutron lens
- 200 mm
- F 3,5-32
- format 46 mm
- M.O.D. 0,85 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount M58-mount

Dimensions 80 mm × 175mm

Max. outer diameter 80 mm (without knurled screws)
90 mm (with knurled screws)

Max. length (excl. thread) 252 mm

Weight ≤ 1228 g

Filter thread M 72,0 × 0,75

Lens data

Lens resolution 48 MP

Focal length 200 mm

Focal range ≥ 50 mm

Format 46 mm

Aperture F3,5-32

Aperture control Manual

M.O.D. 0.85 m