

Overview

- Myutron lens
- 35 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,23 m
- locating screw for aperture and focus
- F-mount



Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount F-Mount

Dimensions 57.5 mm × 84,0 mm

Max. outer diameter 57.5 mm (without knurled screws)
67.5 mm (with knurled screws)

Max. length (excl. thread) 84 mm

Weight ≤ 386 g

Filter thread M 52,0 × 0,75

Lens data

Lens resolution 48 MP

Focal length 35 mm

Focal range ≥ 25 mm ... < 50 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.23 m

Environmental conditions

Operating temperature 0 ... +40 °C