

## ZVL-LSF3528-U58

Article number: 11205385

### Overview

- Myutron lens
- 35 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,23 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



### Technical data

#### General data

Manufacturer Myutron

#### Mechanical data

Lens mount M58-mount

Dimensions 62 mm × 123 mm

Max. outer diameter 62 mm (without knurled screws)  
62 mm (with knurled screws)

Max. length (excl. thread) 118 mm

Weight ≤ 416 g

Filter thread M 52,0 × 0,75

#### Lens data

Lens resolution 48 MP

Focal length 35 mm

Focal range ≥ 25 mm ... < 50 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.23 m

#### Environmental conditions

Operating temperature 0 ... +40 °C