

ZVL-LSF5028-F

Article number: 11201896

Overview

- Myutron lens
- 50 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,19 m
- locating screw for aperture and focus
- F-mount



Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount F-Mount

Dimensions 70 mm × 76.5 mm

Max. outer diameter 70 mm (without knurled screws)
80 mm (with knurled screws)

Max. length (excl. thread) 76.5 mm

Weight ≤ 455 g

Filter thread M 67,0 × 0,75

Lens data

Lens resolution 48 MP

Focal length 50 mm

Focal range ≥ 50 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.19 m

Environmental conditions

Operating temperature 0 ... +40 °C