

ZVL-LSF5028-U58

Article number: 11205386

Overview

- Myutron lens
- 50 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,19 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Picture similar

Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount M58-mount

Dimensions 70 mm × 115 mm

Max. outer diameter 70 mm (without knurled screws)
74 mm (with knurled screws)

Max. length (excl. thread) 111 mm

Weight ≤ 494 g

Filter thread M 67,0 × 0,75

Lens data

Lens resolution 48 MP (suitable for 65 MP)

Focal length 50 mm

Focal range ≥ 50 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.19 m

Environmental conditions

Operating temperature 0 ... +40 °C