

ZVL-M118F1218IRCS

Article number: 11166843

Overview

- Kowa lens
- 12 mm
- F 2,0-16
- format 4/3"
- M.O.D. 0,3 m
- CS-mount



Technical data

General data

Manufacturer Evetar

Mechanical data

Lens mount CS-mount

Dimensions 30 mm × 15,3 mm

Max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

Max. length (excl. thread) 15.3 mm

Lens data

Lens resolution 3 MP

Focal length 12 mm

Focal range $\geq 12 \text{ mm} \dots < 25 \text{ mm}$

Format 1/1.8"

Aperture F1:1,8

Aperture control Manual

M.O.D. 0.3 m