

ZVL-N118F0818IRCSR3

Article number: 11166844

Overview

- Kowa lens
- 8 mm
- F 1,4-16
- format 1"
- M.O.D. 0,2 m
- CS-mount



Technical data

General data

Manufacturer Evetar

Mechanical data

Lens mount CS-mount

Dimensions 30 mm × 21 mm

Max. outer diameter 30 mm (without knurled screws)
40 mm (with knurled screws)

Max. length (excl. thread) 21 mm

Lens data

Lens resolution 3 MP

Focal length 7.8 mm

Focal range < 12 mm

Format 1/1.8"

Aperture F1:1,8

Aperture control Manual

M.O.D. 0.2 m