

**Overview**

- Computer lens
- 8 mm
- F 2,6-16
- format 1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



**Technical data**

**General data**

Manufacturer Computar

**Mechanical data**

Lens mount C-mount

Dimensions 69,5 mm × 52,93 mm

Max. outer diameter 69.5 mm (without knurled screws)  
69.5 mm (with knurled screws)

Max. length (excl. thread) 55.23 mm

Weight ≤ 203 g

**Lens data**

Lens resolution 20 MP

Focal length 8 mm

**Lens data**

Focal range < 12 mm

Format 1"

Aperture F2,6-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 76.9 °

Vertical angle of view 61.5 °

Diagonal angle of view 88.8 °

At image format 12,8 × 9,6 mm

**Environmental conditions**

Operating temperature -10 ... +50 °C