

## Overview

- Computar lens
- 35 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



## Technical data

### General data

Manufacturer Computar

### Mechanical data

Lens mount C-mount

Dimensions 39,5 mm × 45,1 mm

Max. outer diameter 39.5 mm (without knurled screws)  
49.5 mm (with knurled screws)

Max. length (excl. thread) 53.95 mm

Weight ≤ 103 g

Filter thread M 34,0 × 0,5

### Lens data

Lens resolution 12 MP

Focal length 35 mm

### Lens data

Focal range ≥ 25 mm ... < 50 mm

Format 1,1"

Aperture F2,8-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 22.9 °

Vertical angle of view 16.9 °

Diagonal angle of view 28.2 °

At image format 11 × 8 mm

### Environmental conditions

Operating temperature -10 ... +50 °C