

ZVL-Varioptic_C-C-39N0-250-R33

Article number: 11207010

Overview

- Corning® Varioptic® lens
- 25 mm
- F 4-22
- format 2/3"
- M.O.D. 0.12 m
- locating screw for aperture
- C-mount
- UART interface with 6-pin JST connector (3.3 V, 100 mA)



Technical data

General data

Manufacturer Corning

Mechanical data

Lens mount C-mount

Dimensions 36 mm × 47,7 mm

Max. outer diameter 36 mm (without knurled screws)
46 mm (with knurled screws)

Max. length (excl. thread) 47.7 mm

Weight ≤ 116 g

Lens data

Lens resolution 5 MP

Lens data

Focal length 25 mm

Focal range ≥ 12 mm ... < 25 mm

Format 2/3"

Aperture F4-22

Aperture control Manual

M.O.D. 0.12 m

Diagonal angle of view 24.8 °

Environmental conditions

Operating temperature 0 ... +50 °C