

## ZVN-Transceiver SPF+ FS Multi Mode

Article number: 11700593

### overview

- 10 GigE SFP+ Transceiver
- SFP+ module type: Multi Mode Fiber
- SFP-10GSR-85
- max. cable distance 300 m via OM3 multi mode fiber
- wavelength 850 nm



### technical data

#### general data

manufacturer designation SFP-10GSR-85

#### interface

data interface 10 Gigabit Ethernet, Transfer rate 10000 Mb/s/sec, Connector: SFP+ cage

Ethernet type Multi Mode Fiber, 850 nm

#### interface

transfer rate 10 Gb/s

distance max. 300 m

#### environmental conditions

conformity RoHS