

ZVN-Transceiver SPF+ FS Single Mode

Article number: 11700592

overview

- 10 GigE SFP+ Transceiver
- SFP+ module type: Single Mode Fiber
- SFP-10GLR-31
- max. cable distance 10 km via single mode fiber
- wavelength 1310 nm



technical data

general data

manufacturer designation SFP-10GLR-31

interface

data interface 10 Gigabit Ethernet, Transfer rate 10000 Mb/s, Connector: SFP+ cage

Ethernet type Single Mode Fiber, 1310 nm

interface

transfer rate 10 Gb/s

distance max. 10 km

environmental conditions

conformity CE
FCC
RoHS