

# Accessories

## Connectors and cables

### Cable connector M12, 4-pin, on both sides, D-coded, cable



#### Features

- Cable connector M12, 4-pin, for EtherNet encoder
- With shielded cable
- Cable for flexible cable carriers
- Protection IP 67

#### Part number

|          |  |
|----------|--|
| 11034355 | Cable connector M12, 4-pin, on both sides, D-coded, 5 m cable (Z 185.E05)  |
| 11202545 | Cable connector M12, 4-pin, on both sides, D-coded, 1 m cable (Z 185.E01)  |
| 11202549 | Cable connector M12, 4-pin, on both sides, D-coded, 2 m cable (Z 185.E02)  |
| 11202560 | Cable connector M12, 4-pin, on both sides, D-coded, 10 m cable (Z 185.E10) |

#### Technical data

|                         |  |
|-------------------------|--|
| Nominal voltage         | 250 V  |
| Nominal current         | 4 A  |
| Cable length            | 1 m, 2 m, 5 m, 10 m<br>(further length upon request) |
| Operating temperature   | -25...+80 °C   |
| Protection DIN EN 60529 | IP 67  |
| Material                | Cable sheath: PUR green,<br>halogen free             |

#### Suitable for

EAL580-B, EAL580-SC, EAL580-SV, EAL580-T,  
EAM580-K, EAM580-SC, EAM580-SY, G0AMH, G0MMH,  
GBAMH, GBAMS, GBAMW, GBMMH, GBMMS, GBMMW,  
GXAMS, GXAMW, GXMMS, GXMMW

#### Dimensions

