Accessories Connectors and cables

Female connector M23, 12-pin, stainless steel



Features

- Female connector M23 with screwable nut
- With cable (shielded) in different lengths
- Cable version: shield is placed onto the connector housing
- Cable for flexible cable carriers
- Halogen-free
- UL/CSA certification

Part	number
rait	numper

11034361	Female connector M23, 12-pin, stainless steel, without cable (Z 189.001)
11034362	Female connector M23, 12-pin, stainless steel, 10 m cable (Z 189.007)

Suitable for

GE244, GE404


Technical data	
Voltage supply	<250 V
Cable length	10 m (further length upon request)
Cable type	UNITRONIC-FD CP (TP) plus UL/CSA 5x2x0.14 mm² (shielded, twisted pair)
Bending radius	7.5 x cable diameter
Outer diameter	7.5 mm
Operating temperature	-40+80 °C
Material	Cable sheath: PUR grey

Terminal assignment

Connector	Core colour	
Pin 1	brown	
Pin 2	white	
Pin 3	blue	
Pin 4	green	
Pin 5	grey	
Pin 6	yellow	
Pin 7	red	
Pin 8	red/blue	
Pin 9	pink	
Pin 10	violet	
Pin 11	black	
Pin 12	grey/pink	
Color code a	Color code according to DIN 47100.	

Cores twisted in pairs: white-brown, green-yellow, grey-pink, blue-red, black-violet, grey/pink-red/blue

Dimensions



27/11/2018 Subject to modification in technic and design.	Erro
Subject to modificatic	design.
Subject to modificatic	and
Subject to modificatic	technic
Subject to modificatic	.⊑
Subje	modification
27/11/2018	Subject to
	27/11/2018

ors and omissions excepted.