Accessories

Connectors and cables

Female connector M12, 5-pin, A-coded



Features

- Female connector M12 with screwable nut
- With cable (shielded) in different lengths

Part number			
11034356	Female connector M12, 5-pin, A-coded, 5 m cable (Z 185.P05)		
11212237	Female connector M12, 5-pin, A-coded, 10 m cable (Z 185.P10)		

Suitable for EAL580-B, EAL580-SC, EAL580-SV, EAL580-T

Technical data			
Nominal voltage	60 V		
Cable length	5 m, 10 m (further length upon request)		
Ambient temperature	-25+80 °C		
Protection DIN EN 60529	IP 67 (mounted)		
Material	Cable sheath: PUR black, halogen free		

Terminal assignment		
Pin	Core colour	
1	brown	
2	white	
3	blue	
4	black	
5	grey	

Dimensions



