ZVI-HILIGHT80_24VDC_WEIß

HI-LIGHT-80 white 24VDC with M8 connector

Article number: 11130181

overview

- flashable LED back light
- white
- diffuse
- radiation angle 80°
- diameter: 94 mm
- M8/4-pin connector
- dimensions: 87 mm × 87 mm × 20 mm housing




technical data

general data	
manufacturer	Büchner Lichtsysteme GmbH
illumination data	
color	white
illumination characteristic	diffuse
electrical data	
number of poles	4
illumination connector	• M8 connector
current	0,35 A
current at flash mode	≤ 0,8 A
voltage at flash mode	≤ 48 V DC

electrical data	
duty cycle	0-10%
maximum flash duration	1 ms
mechanical data	
construction design	back light
dimensions	87 mm × 87 mm × 20 mm
material of cover glass	acrylic
weight	≤ 180 g
material	aluminum (shot-peened, anodized)
environmental conditions	
operating temperature	max. 50 °C

dimension drawing




2020-01-22 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.

ZVI-HILIGHT80_24VDC_WEIß

HI-LIGHT-80 white 24VDC with M8 connector

Article number: 11130181

pin assignment



M8	signal
1:	LED +24V (pulsing 24-48 V)
2:	N.C.
3:	LED - (GND)
4:	N.C.

2020-01-22 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.