Obj Cinegon 1,4/8-0902

Article number: 11035932

overview

- Schneider Kreuznach lens
- 8 mm
- F 1,4-11
- format 2/3"
- M.O.D. 0.072 m
- C-mount



technical data

general data	
manufacturer	Schneider Kreuznach
mechanical data	
lens mount	C-mount
dimensions	34 mm × 37,5 mm
max. outer diameter	34 mm (without knurled screws) 50 mm (with knurled screws)
max. length (excl. thread)	37,5 mm
weight	≤ 134 g
filter thread	M 30,5 × 0,5

lens data	
lens resolution	5 MP
focal length	8 mm
focal range	< 12 mm
format	2/3″
aperture	F1,4-11
aperture control	manual
M.O.D.	0,072 m
environmental conditions	
storage temperature	-25 … +70 °C

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.