Obj Cinegon 1,8/16-0901

Article number: 11076106

overview

- Schneider Kreuznach lens
- 16 mm
- F 1,8-22
- format 1"
- M.O.D. 0,155 m
- C-mount



technical data

general data	
manufacturer	Schneider Kreuznach
mechanical data	
lens mount	C-mount
dimensions	34 mm × 44,8 mm
max. outer diameter	34 mm (without knurled screws) 44 mm (with knurled screws)
max. length (excl. thread)	40,9 mm
weight	≤ 102 g
filter thread	M 30,5 × 0,5

lens data	
lens resolution	5 MP
focal length	16 mm
focal range	≥ 12 mm … < 25 mm
format	1″
aperture	F1,8-22
aperture control	manual
M.O.D.	0,155 m
environmental conditions	
storage temperature	-25 … +70 °C

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.