Obj LINOS MeVis C 50mm/f1,8

Article number: 11051406

overview

- Linos lens
- 50 mm
- F 1,8-16
- format 1"
- M.O.D. 0,67 m
- C-mount



technical data

general data	
manufacturer	Linos
mechanical data	
lens mount	C-mount
dimensions	42 mm × 67,5 mm
max. outer diameter	42 mm (without knurled screws) 52 mm (with knurled screws)
max. length (excl. thread)	67,5 mm
weight	≤ 240 g
filter thread	M 35,5 × 0,5

lens data	
lens resolution	20 MP
focal length	50 mm
focal range	≥ 50 mm
format	1″
aperture	F1,8-16
aperture control	manual
M.O.D.	0,67 m

2020-01-27 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.